

FDM TPU 92A

FDM® TPU 92A is a thermoplastic polyurethane with a Shore A value of 92. The material exhibits high elongation, superior toughness, durability and abrasion resistance.

FDM TPU 92A brings the benefits of elastomers to FDM 3D printing and offers the capability to quickly produce large and complex elastomer parts. Typical applications include flexible hoses, tubes, air ducts, seals, protective covers and vibration dampeners.

FDM TPU 92A is available on the F123 and F123CR (composite-ready) Series 3D printers and is compatible with QSR™ soluble support material.

Mechanical Properties	Test Method	Value	
		XY Orientation	XZ Orientation
Shore Hardness (molded)	ASTM D2240	92 Shore A	92 Shore A
Tensile Strength, Yield (Type 1, 0.125", 0.2"/min)	ASTM D412	15.6 MPa (2,265 psi)	16.1 MPa (2,332 psi)
Tensile Strength, Ultimate (Type 1, 0.125", 0.2"/min)	ASTM D412	16.8 MPa (2,432 psi)	17.4 MPa (2,519 psi)
Tensile Modulus (Type 1, 0.125", 0.2"/min)	ASTM D412	15.3 MPa (2,212 psi)	20.7 MPa (3,000 psi)
Elongation at Break (Type 1, 0.125", 0.2"/min)	ASTM D412	552%	482%
Elongation at Yield (Type 1, 0.125", 0.2"/min)	ASTM D412	466%	385%
Tensile Stress at 100% Elongation (PSI)	ASTM D412	6.9 MPa (999 psi)	7.6 MPa (1,096 psi)
Tensile Stress at 300% Elongation (PSI)	ASTM D412	11.0 MPa (1,598 psi)	11.9 MPa (1,722 psi)
Flexural Strength (Method 1, 0.05"/min)	ASTM D790	1.8 MPa (255 psi)	2.4 MPa (351 psi)
Flexural Modulus (Method 1, 0.05"/min)	ASTM D790	25.6 MPa (3,719 psi)	36.9 MPa (5,349 psi)
Flexural Strain at Break (Method 1, 0.05"/min)	ASTM D790	No break	No break
Tear Strength - Stamped	ASTM D624-C	84.6 N/mm (483 lbF/in)	NA
Compressive Strength, Yield (Method 1, 0.05"/min)	ASTM D695	2.6 MPa (384 psi)	2.6 MPa (384 psi)
Compressive Strength, Ultimate (Method 1, 0.05"/min)	ASTM D695	2.6 MPa (384 psi)	2.6 MPa (384 psi)
Compressive Modulus (Method 1, 0.05"/min)	ASTM D695	16.9 MPa (2,457 psi)	16.9 MPa (2,457 psi)
Compression Set at 22 Hours @ 23 °C	ASTM D395	21%	NA
Compression Set at 22 Hours @ 70 °C	ASTM D395	44%	NA

FDM TPU 92A

Thermal Properties	Test Method	Value
Heat Deflection (HDT) @ 66 psi	ASTM D648	38 °C (100.4 °F)
Heat Deflection (HDT) @ 15 psi	NA	56 °C (132.8 °F)
Vicat Softening Temperature (Rate B/50)	ASTM D1525	95 °C (203 °F)
Glass Transition Temperature (T _g)	DMA (SSYS)	-42 °C (-43.6 °F)
Coefficient of Thermal Expansion (x-direction)	ASTM E831	139 µm/(m·°C) (7.72E-05 in/(in·°F))
Coefficient of Thermal Expansion (y-direction)	ASTM E831	159 µm/(m·°C) (8.83E-05 in/(in·°F))
Coefficient of Thermal Expansion (z-direction)	ASTM E831	176 µm/(m·°C) (9.78E-05 in/(in·°F))

Electrical Properties	Test Method	Value	
		XY Orientation	XZ Orientation
Volume Resistivity	ASTM D257	6.09E+10 ohm-cm	7.17E+13 ohm-cm

Other	Test Method	Value
Specific Gravity	ASTM D792	1.13502

The information presented are typical values intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. End-use material performance can be impacted (+/-) by, but not limited to, part design, end-use conditions, test conditions, etc. Actual values will vary with build conditions. Tested parts were built on a Stratasys F370™ @ 0.010" (0.254 mm) slice.

The performance characteristics of these materials may vary according to application, operating conditions or end use. Each user is responsible for determining that the Stratasys material is safe, lawful and technically suitable for the intended application, as well as for identifying the proper disposal (or recycling) method consistent with applicable environmental laws and regulations. Stratasys makes no warranties of any kind, express or implied, including, but not limited to, the warranties of merchantability, fitness for a particular use or warranty against patent infringement.

USA - Headquarters

7665 Commerce Way
Eden Prairie, MN 55344, USA
+1 952 937 3000

ISRAEL - Headquarters

1 Holtzman St., Science Park
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000

EMEA

Airport Boulevard B 120
77836 Rheinmünster, Germany
+49 7229 7772 0

ASIA PACIFIC

7th Floor, C-BONS International Center
108 Wai Yip Street Kwun Tong Kowloon
Hong Kong, China
+ 852 3944 8888



GET IN TOUCH.

www.stratasys.com/contact-us/locations

stratasys.com

ISO 9001:2008 Certified

