



Hydraulic line clamp for the F-16

The U.S. Air Force increasingly faces challenges with providing components for aging vehicles. The Origin One and LOCTITE® 3955 were used to create a replacement clamp for the F-16 aircraft that could withstand the vibrations, high heat, and chemical exposure required to be flight safe and pass UL 94 V-0 testing. The two halves, which were made with 3955, were then tethered with a flexible band printed with LOCTITE® IND402 to increase efficiency of installation. The final, optimized clamp design employed on F-16 aircraft doubled the strength of the original part while weighing less.

Hydraulic line clamp for the F-16

System	Stratasys Origin One
Material	LOCTITE 3955 and LOCTITE IND402
Support Material Amount Used	None

ISO 9001:2015 Certified

© 2021 Stratasys Ltd. All rights reserved. Stratasys, Stratasys signet and Origin are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries or affiliates and may be registered in certain jurisdictions. All other trademarks belong to their respective owners. Product specifications subject to change without notice. PC_P3_Hydraulic line clamp_0921a

STRATASYS.COM

