

# Fortus 380mc and 450mc



## Get the latest FDM technology for advanced prototyping and production.

Bring the speed, agility and design freedom of advanced additive manufacturing to your business while gaining the latest advances in FDM® technology. The Fortus 380mc™ and Fortus 450mc™ 3D Production Systems build high-requirement prototypes, rugged jigs, fixtures and tooling, and custom production parts in familiar thermoplastics. And these 3D production systems are engineered for ease of use, including an all-new, intuitive touchscreen interface for smooth workflow. Both let you choose materials individually or in economical bundles.

**Fortus 380mc:** Quickly build advanced prototypes and production aids as large as 355 x 305 x 305 mm (14 x 12 x 12 in.) in eight standard and engineering thermoplastics.

**Fortus 450mc:** Get all the capabilities of the Fortus 380mc, plus a larger build envelope (406 x 355 x 406 mm [16 x 14 x 16 in.]) and the option to run high-performance thermoplastics for specialized production parts in demanding fields such as medical, aerospace, research and defense.

### System Specifications

Build Envelope (XYZ)	<b>380mc:</b> 355 x 305 x 305 mm (14 x 12 x 12 in.)	<b>450mc:</b> 406 x 355 x 406 mm (16 x 14 x 16 in.)
Material Delivery	<b>380mc:</b> One bay each for material and support canisters	<b>450mc:</b> Two bays each for material and support canisters. Auto changeover between canisters

### Material Options

Material	Layer Thickness				Support Structure	Available Colors	
	0.330 mm (0.013 in.)	0.254 mm (0.010 in.)	0.178 mm (0.007 in.)	0.127 mm (0.005 in.)			
ABS-ESD7™	○	●	●	○	Soluble	■ Black	
ABS-M30™	●	●	○	●	Soluble	■ Ivory ■ Black ■ Blue	□ White ■ Red ■ Dark Gray
ABS-M30i™	●	●	●	●	Soluble	■ Ivory	
Antero™ 800NA*	○	●	○	○	Breakaway	■ Natural	
Antero 840CN03*	○	●	○	○	Breakaway	■ Natural	
ASA	●	●	●	●	Soluble	■ Black ■ Dark Gray ■ Light Gray □ White ■ Ivory	■ Dark Blue ■ Green ■ Yellow ■ Orange ■ Red
FDM Nylon 12™	●	●	●	○	Soluble	■ Black	
FDM Nylon 12CF™*	○	●	○	○	Soluble	■ Black	
PC	●	●	●	●	Breakaway, Soluble	□ White	
PC-ABS	●	●	●	●	Soluble	■ Black	
PC-ISO™	●	●	●	○	Breakaway	■ Translucent Natural □ White	
ULTEM™ 9085 resin*	●	●	○	○	Breakaway	■ Tan ■ Black	
ULTEM™ 1010 resin*	●	●	○	○	Breakaway	■ Natural	
ST-130*	●	○	○	○	Breakaway	■ Tan	

\*Fortus 450mc only

# Fortus 380mc and 450mc



## Other Specifications

System Size and Weight	129.5 cm x 90.2 cm x 198.4 cm (51 x 35.5 x 78.1 in.) 601 kg (1325 lbs.)
Achievable Accuracy	Parts are produced within an accuracy of $\pm .127$ mm ( $\pm .005$ in.) or $\pm .0015$ mm/mm ( $\pm .0015$ in/in), whichever is greater). Z part accuracy includes an additional tolerance of $-0.000/+$ slice height. Note: Accuracy is geometry dependent. Achievable accuracy specification derived from statistical data at 95% dimensional yield.
Network Communication	10/100 base T connection. Ethernet protocol.
Operator Attendance	Limited attendance for job start and stop required.
Power Requirements	208VAC 3 phase, 50/60 Hz, consumes 18 Amps
Regulatory Compliance	CE, cTUVus, EAC, FCC Part B
Software	All Fortus systems include Insight™ and Control Center™ job processing and management software. Compatible with GrabCAD Print for use with job reports, scheduling and remote monitoring.
Operating System	Microsoft Windows 10 (Pro, Enterprise, Education), Microsoft Windows 8.1 and Windows 8 (Pro, Enterprise), Microsoft Windows 7 (Pro, Enterprise, Ultimate), Microsoft Windows Server 2012 R2. Insight software requires a 64-bit operating system.

### USA - Headquarters

7665 Commerce Way  
Eden Prairie, MN 55344, USA  
+1 952 937 3000

### ISRAEL - Headquarters

1 Holtzman St., Science Park  
PO Box 2496  
Rehovot 76124, Israel  
+972 74 745 4000

[stratasys.com](http://stratasys.com)

ISO 9001:2015 Certified

### EMEA

Airport Boulevard B 120  
77836 Rheinmünster, Germany  
+49 7229 7772 0

### ASIA PACIFIC

7th Floor, C-BONS International Center  
108 Wai Yip Street Kwun Tong Kowloon  
Hong Kong, China  
+ 852 3944 8888



**GET IN TOUCH.**

[www.stratasys.com/contact-us/locations](http://www.stratasys.com/contact-us/locations)

