



End-of-Arm Soft Gripper

Featuring the brand new P3 Stretch 475 material printed on the Origin One, these soft-grippers make use of the compression and high-rebound capability of the material, which features 200% elongation at break and 47A hardness. This solution is perfect for operations making high-finish parts that require soft contact that leaves no trace. This soft gripper is a great end-use solution or a stop gap part to help keep production workflows on track. In just over 3 printing hours, a single Origin One machine can produce 6 grippers that can be post-processed and installed on the shop floor in just 20 minutes.

System	Stratasys Origin One
Material	P3 Stretch 475
Build Time	3h for 6 parts/20m post-processing
Material Amount Used	97cc for 6 parts

ISO 9001:2015 Certified

© 2022 Stratasys. All rights reserved. Stratasys, Stratasys signet and Origin One™ are trademarks or registered trademarks of are registered trademarks of Stratasys Inc. All other trademarks are the property of their respective owners and Stratasys assumes no responsibility with regard to the selection, performance, or use of these non- Stratasys products. Product specifications subject to change without notice. PC-small_P3_Soft Gripper_0822a

STRATASYS.COM

