



Origin One Door Seal

Engineers at leading automotive companies use Origin One to test fit and function of their designs throughout the product development process. A consistent challenge is the ability to print flexible parts that closely resemble the performance of injection molded final product. Using Loctite™ IND 402 door seals and other flexible parts are able to be fit and tested on pre-production versions of car models. IND 402 has fantastic elongation at break at over 200%, which gives it great characteristics for door seal testing in all phases of the automotive development process.

System	Stratasys Origin One
Material	IND402
Build Time	13h 18m
Model Material Used	191 CC

ISO 9001:2015 Certified

© 2022 Stratasys Ltd. All rights reserved. Stratasys, Stratasys signet and Origin are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries or affiliates and may be registered in certain jurisdictions. All other trademarks belong to their respective owners. Product specifications subject to change without notice. PC_P3_Door Seal_1022a

STRATASYS.COM